




CHANGE	
DATE: 2008-12-10	DRN: J.S.
SCALE: NTS	APPV'D:
DISK:	FILE:
PROJECT: System Configurations (PLM)	
DRAWING: 12 Metrix, 4 Subs (flown)	
Plot: 1/2 (System)	Issue: 1




ADAMSON SYSTEMS ENGINEERING
1401 Scugog Line 6
Port Perry, ONTARIO, L9L 1B2
TEL:(905)982-0520 FAX:(905)982-0609



	LOW L	HIGH L	SUB L
PLM10000Q			
Amp 1	CH A	CH B	CH C / CH D
Gain=29dB VPL 141V			
	LOW R	HIGH R	SUB R
PLM10000Q			
Amp 2	CH A	CH B	CH C / CH D
Gain=29dB VPL 141V			

Note: Metrix Subs cannot be operated in cardioid mode using Dolby Lake proc.

CHANGE	
DATE: 2008-12-10	DRN: J.S.
SCALE: NTS	APPV'D:
DISK:	FILE:
PROJECT: System Configurations (PLM)	
DRAWING: 12 Metrix, 4 Subs (flown)	
Plot: 2/2 (Amp Rack)	Issue: 1



ADAMSON SYSTEMS ENGINEERING
1401 Scugog Line 6
Port Perry, ONTARIO, L9L 1B2
TEL:(905)982-0520 FAX:(905)982-0609

