




CHANGE	
DATE: 2008-12-10	DRN: J.S.
SCALE: NTS	APPV'D:
DISK:	FILE:
PROJECT: System Configurations (PLM)	
DRAWING: 6 Metrix, 2 Subs (stack)	
Plot: 1/2 (System)	Issue: 1



ADAMSON SYSTEMS ENGINEERING
 1401 Scugog Line 6
 Port Perry, ONTARIO, L9L 1B2
 TEL:(905)982-0520 FAX:(905)982-0609



CHANGE

DATE: 2008-12-10 DRN: J.S.

SCALE: NTS APPV'D:

DISK: FILE:

PROJECT:
System Configurations (PLM)

DRAWING:
6 Metrix, 2 Subs (stack)

Plot: 2/2 (Amp Rack)

Issue: 1



ADAMSON SYSTEMS ENGINEERING
1401 Scugog Line 6
Port Perry, ONTARIO, L9L 1B2
TEL:(905)982-0520 FAX:(905)982-0609

	LOW	HIGH	SUB
PLM10000Q			
Amp 1	CH A	CH B	CH C / CH D
Gain=29dB VPL 141V			

Note: Metrix Subs cannot be operated in cardioid mode using Dolby Lake proc.

